



COBRA CUFF®

APPLICATION INSTRUCTIONS

MILSPEC
PLASTICS

NSN No. 8465-01-676-2327

CAGE CODE No. 68D01

PART No. MS24D-250

COBRA CUFF APPLICATION

Patented Cobra Cuffs are the only rubber based, disposable restraint which comes fully assembled and has a unique Double Lock. The Double Lock provides additional strength and helps prevent accidental over tightening during arrest or transport -as well as tampering or shimming of the locking mechanism.

To Apply Cobra Cuffs;

- First instruct the compliant subject to place their hands behind their back, palms facing outward in the prone position and insert hands into restraint openings.
- Insert your finger into riveted strap loop and pull straight back to tighten. To ensure easy application: Ensure that one hand is on the center locking block as you pull one strap to fully tighten. Adjust tension on each wrist to comfortable but secure position. Then depress Double Lock as far as it will go for each wrist.

COBRA CUFF REMOVAL

Milspec Plastics recommends using the patented Cobra Cutter for easy removal of the Cobra Cuffs. Note: You can use any type of cutting tool that your agency approves. Gain control of the Cobra Cuff where you feel comfortable. Insert the blade of the cutter below the Locking Block. Apply pressure and push the cutter forward, cutting the Cobra Cuff strap in half. Apply in the same manner to the other secured cuff.

Reminder: This is not a substitute for practical training. Please follow your department SOP when applying or training with this restraint or any other restraining device.

Please review the Practical application video at www.milspecplastics.com under the download section.



DIVISION OF CS SYSTEMS COMPANY, INC

MILSPEC PLASTICS | 28 Schenck Parkway, Ste 200 | Asheville, NC 28803 | 800-525-9878 | MILSPECPLASTICS.COM